

Product data sheet

Characteristics

ISM20609

OptiLine 70, post, two-sided, natural, 613 mm



Main

Range of product	OptiLine 70
Cabling installation system	Post
Product type	Post
Type of post	Two-sided
Pole/post surface finish	Anodized

Complementary

Colour	Natural
Fixing mode	Screw-fixed
Front opening size	70 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	613 mm
Width	164 mm
Market segment	Residential Small commercial





Environment

Standards	73/23/EEC 93/68/EEC EN-AW-6063 IEC 1084-2-4 SS 424 10 32
Operating temperature	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.4 cm
Package 1 Width	16.4 cm
Package 1 Length	61.3 cm
Package 1 Weight	1.42 kg
Unit Type of Package 2	P12
Number of Units in Package 2	12
Package 2 Height	62.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	29.04 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------