

## Product data sheet

### Characteristics

# ISM20609

OptiLine 70 - post - two-sided - natural - 613 mm



### Main

|                             |             |
|-----------------------------|-------------|
| Range of product            | OptiLine 70 |
| Cabling installation system | Post        |
| Product type                | Post        |
| Type of post                | Two-sided   |
| Pole/post surface finish    | Anodized    |

### Complementary

|                           |                                 |
|---------------------------|---------------------------------|
| Colour                    | Natural                         |
| Fixing mode               | Screw-fixed                     |
| Front opening size        | 70 mm                           |
| Material                  | Aluminium anodized              |
| Quantity package 1 / unit | Set of 1                        |
| Height                    | 613 mm                          |
| Width                     | 164 mm                          |
| Market segment            | Residential<br>Small commercial |

### Environment

|                         |  |
|-------------------------|--|
| Standards               | 73/23/EEC<br>93/68/EEC<br>EN-AW-6063<br>IEC 1084-2-4<br>SS 424 10 32 |
| Operating temperature   | -25...60 °C  |
| IP degree of protection | IP40   |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Weight             | 1.42 kg  |
| Package 1 Height             | 15.4 cm  |
| Package 1 width              | 16.4 cm  |
| Package 1 Length             | 61.3 cm  |
| Unit Type of Package 2       | P12      |
| Number of Units in Package 2 | 12       |
| Package 2 Weight             | 29.04 kg |
| Package 2 Height             | 62 cm    |
| Package 2 width              | 80 cm    |
| Package 2 Length             | 120 cm   |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| RoHS exemption information | <a href="#">Yes</a>  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|