

# Product data sheet

## Characteristics

# ISM20652

## floor fixing, OptiLine 70, grey

### Main

Cabling installation system	Pole Post
Product or component type	Floor fixing

### Complementary

Type of pole	One-sided
Type of post	One-sided
Colour tint	Grey (RAL 9007)
Quantity per set	Set of 1
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted
Fixing mode	By screws
Material	Aluminium powder coated
Length	153 mm
Height	45 mm
Width	100 mm
Market segment	Small commercial Residential

### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10 cm
Package 1 Width	4.5 cm
Package 1 Length	15.3 cm
Package 1 Weight	250 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	39.8 cm
Package 2 Width	30 cm
Package 2 Length	29.9 cm
Package 2 Weight	8.23 kg
Unit Type of Package 3	PAL

Number of Units in Package 3	240
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	85.84 kg

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------