

Product data sheet

Characteristics

ISM20653

OptiLine 70 - floor fixing - grey



Main

Cabling installation system	Post Pole
Product or component type	Floor fixing

Complementary

Type of pole	Two-sided
Type of post	Two-sided
Colour tint	Grey (RAL 9007)
Quantity per set	Set of 1
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted
Fixing mode	By screws
Material	Aluminium powder coated
Length	154 mm
Height	45 mm
Width	164 mm
Market segment	Small commercial Residential

Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.4 cm
Package 1 Width	4.5 cm
Package 1 Length	15.4 cm
Package 1 Weight	336 g
Unit Type of Package 2	CAR
Number of Units in Package 2	30
Package 2 Height	39.8 cm
Package 2 Width	30 cm
Package 2 Length	29.9 cm
Package 2 Weight	10.93 kg
Unit Type of Package 3	PAL

Number of Units in Package 3	240
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	107.44 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------