

Product data sheet

Characteristics

ISM20660

OptiLine 70 - floor feeder - natural



Main

Cabling installation system	Post Pole
Product or component type	Floor feeder

Complementary

Type of pole	One-sided Two installation boxes Two-sided One installation box
Type of post	Two-sided One-sided
Colour tint	Natural
Quantity per set	Set of 1
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Tension-mounted
Fixing mode	By screws
Material	Aluminium anodized
Length	2500 mm
Height	18 mm
Width	91 mm
Market segment	Residential Small commercial

Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.47 kg
Package 1 Height	9.1 cm
Package 1 width	1.8 cm
Package 1 Length	250 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------