

Product data sheet

Characteristics

ISM20808

foot, OptiLine 45, grey



Main

Cabling installation system	Pole
Product or component type	Foot

Complementary

Type of pole	One-sided Two-sided
Colour tint	Grey (RAL 9007)
Quantity per set	Set of 1
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Free-standing
Fixing mode	Free-standing
Material	Cast iron painted
Height	29 mm
Diameter	317 mm
Market segment	Small commercial Residential

Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	31.7 cm
Package 1 Length	31.7 cm
Package 1 Weight	10.75 kg
Unit Type of Package 2	P12
Number of Units in Package 2	62
Package 2 Height	80 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	681.724 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------