

## Product data sheet

### Characteristics

# ISM20808

## OptiLine 45 OptiLine 70 - foot - grey



### Main

Cabling installation system	Pole
Product or component type	Foot

### Complementary

Type of pole	One-sided Two-sided
Colour tint	Grey (RAL 9007)
Quantity per set	Set of 1
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Free-standing
Fixing mode	Free-standing
Material	Cast iron painted
Height	29 mm
Diameter	317 mm
Market segment	Small commercial Residential

### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	10.824 kg
Package 1 Height	2.9 cm
Package 1 width	31.7 cm
Package 1 Length	31.7 cm
Unit Type of Package 2	P12
Number of Units in Package 2	62
Package 2 Weight	725 kg
Package 2 Height	80 cm
Package 2 width	80 cm
Package 2 Length	120 cm

## Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------