

# Product data sheet

## Characteristics

# ISM20809

## OptiLine 45, foot, grey



### Main

Cabling installation system	Pole
Product or component type	Foot

### Complementary

Type of pole	One-sided
Colour tint	Grey (RAL 9007)
Quantity per set	Set of 1
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Free-standing
Fixing mode	Free-standing
Material	Cast iron painted
Length	346 mm
Height	33 mm
Width	250 mm
Market segment	Residential Small commercial





### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	34.0 cm
Package 1 Length	35.5 cm
Package 1 Weight	10.729 kg
Unit Type of Package 2	S04
Number of Units in Package 2	1
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	11.566 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------