

## Product data sheet

### Characteristics

# ISM20816

## OptiLine 45, ceiling fixing, white



### Main

Cabling installation system	Pole Service box
Product or component type	Ceiling fixing

### Complementary

Type of pole	Two installation boxes Two-sided One-sided One installation box
Type of service box	Service box kit
Device presentation	Empty
Colour tint	White (RAL 9010)
Quantity per set	Set of 1
Product compatibility	Altira wiring device Unica wiring device
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Free-standing
Fixing mode	By screws
Material	Aluminium powder coated
Length	90 mm
Height	50 mm
Width	156 mm
Market segment	Residential Small commercial

### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	9.100 cm
Package 1 Length	15.600 cm
Package 1 Weight	120.0 g
Unit Type of Package 2	S03

Number of Units in Package 2	30
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.087 kg

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------