

Product data sheet

Characteristics

ISM20816

OptiLine 45 OptiLine 70 - ceiling fixing - white



Main

| | |
|-----------------------------|------------------|
| Cabling installation system | Pole Service box |
| Product or component type | Ceiling fixing |

Complementary

| | |
|--------------------------|--|
| Type of pole | Two installation boxes Two-sided One-sided One installation box |
| Type of service box | Service box kit |
| Device presentation | Empty |
| Colour tint | White (RAL 9010) |
| Quantity per set | Set of 1 |
| Product compatibility | Altira wiring device Unica wiring device |
| Pole/post surface finish | Anodized Powder coated |
| Pole fixing mode | Free-standing |
| Fixing mode | By screws |
| Material | Aluminium powder coated |
| Length | 90 mm |
| Height | 50 mm |
| Width | 156 mm |
| Market segment | Residential Small commercial |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...60 °C |
| IP degree of protection | IP30 |

Offer Sustainability

| | |
|----------------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |

Contractual warranty

Warranty

18 months
