

Product data sheet

Characteristics

ISM20817

floor feeder, OptiLine 45, grey



Main

Cabling installation system	Pole Post
Product or component type	Floor feeder

Complementary

Type of pole	One-sided Two installation boxes Two-sided One installation box
Type of post	One-sided Two-sided
Colour tint	Grey (RAL 7030)
Quantity per set	28 m
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Tension-mounted
Fixing mode	By screws
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	18 mm
Width	75 mm
Market segment	Small commercial Residential

Environment

Standards	EN 50085-1:2005 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Height	2.0 cm
Package 1 Width	8.5 cm
Package 1 Length	200.0 cm
Package 1 Weight	1.06 kg
Unit Type of Package 2	BB1

Number of Units in Package 2	28
Package 2 Height	9.0 cm
Package 2 Width	21.0 cm
Package 2 Length	202.0 cm
Package 2 Weight	15.0 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	448
Package 3 Height	65.0 cm
Package 3 Width	120.0 cm
Package 3 Length	210.0 cm
Package 3 Weight	261.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------