

Product data sheet

Characteristics

ISM20818

jointing piece, OptiLine 45, grey

Main

Cabling installation system	Post Pole
Product or component type	Jointing piece

Complementary

Type of pole	Two-sided One installation box Two installation boxes One-sided
Type of post	One-sided Two-sided
Colour tint	Grey (RAL 7030)
Quantity per set	Set of 10
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Tension-mounted
Material	PVC (polyvinyl chloride)
Length	78 mm
Height	20 mm
Width	50 mm
Market segment	Small commercial Residential

Environment

Standards	EN 50085-1:2005 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 cm
Package 1 Width	5.0 cm
Package 1 Length	7.97 cm
Package 1 Weight	12.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	8.6 cm

Package 2 Width	5.5 cm
Package 2 Length	12.0 cm
Package 2 Weight	130.0 g
Unit Type of Package 3	S03
Number of Units in Package 3	300
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	4.087 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------