

Product data sheet

Characteristics

ISM20822

OptiLine 45 OptiLine 70 - decorative stripe - grey



Main

Cabling installation system	Post Pole
Product or component type	Decorative stripe

Complementary

Type of pole	One-sided Two-sided
Type of post	One-sided Two-sided
Colour tint	Grey (RAL 7043)
Quantity per set	5 m
Pole/post surface finish	Powder coated Anodized
Pole fixing mode	Tension-mounted Free-standing
Material	Silicone rubber
Length	5000 mm
Diameter	3.5 mm
Market segment	Small commercial Residential

Environment

Standards	EN 50085-1:2005 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

Packing Units

Package 1 Weight	12.000 g
Package 1 Height	1.000 mm
Package 1 width	1000.000 mm
Package 1 Length	3.000 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------