

Product data sheet

Characteristics

ISM20823

OptiLine 50 - decorative stripe - white



Main

Cabling installation system	Post Pole
Product or component type	Decorative stripe

Complementary

Type of pole	Two-sided One-sided
Type of post	One-sided Two-sided
Colour tint	White (RAL 9010)
Quantity per set	5 m
Pole/post surface finish	Powder coated Anodized
Pole fixing mode	Tension-mounted Free-standing
Material	Silicone rubber
Length	5000 mm
Diameter	3.5 mm
Market segment	Residential Small commercial

Environment

Standards	EN 50085-1:2005 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

Packing Units

Package 1 Weight	12.000 g
Package 1 Height	1.000 mm
Package 1 width	1000.000 mm
Package 1 Length	3.000 mm

Contractual warranty

Warranty	18 months
----------	-----------