

## Product data sheet

### Characteristics

# ISM20823

## OptiLine 45, decorative stripe, white



### Main

Cabling installation system	Post Pole
Product or component type	Decorative stripe

### Complementary

Type of pole	Two-sided One-sided
Type of post	One-sided Two-sided
Colour tint	White (RAL 9010)
Quantity per set	5 m
Pole/post surface finish	Powder coated Anodized
Pole fixing mode	Tension-mounted Free-standing
Material	Silicone rubber
Length	5000 mm
Diameter	3.5 mm
Market segment	Residential Small commercial

### Environment

Standards	EN 50085-1:2005 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	100 cm
Package 1 Length	0.3 cm
Package 1 Weight	12 g

### Contractual warranty

Warranty	18 months
----------	-----------