

Product data sheet

Characteristics

KBA25ED2305

Straight length, Canalis KBA, 25 A, 1 circuit L +N+PE, 5 tap-off units, 3 m



Main

Range of product	Canalis
Product or component type	Busbar trunking
Product compatibility	KBA

Complementary

Device application	Lighting Power socket distribution
Maximum radiated magnetic field	2 pT
[Ue] rated operational voltage	230...400 V
[Uimp] rated impulse withstand voltage	4 kV
[Ui] rated insulation voltage	690 V
[Ie] rated operational current	25 A at 35 °C
Network frequency	50/60 Hz
[Icw] rated short-time withstand current	0.44 kA
[Ipk] rated peak withstand current	4.4 kA
Thermal stress limit	195 kA ² .s
THDI	0...15 % 25 A 15...33 % 20 A 33...100 % 16 A
Maximum voltage drop	<0.72 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.67 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.61 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.54 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Mounting mode	By clips
Busbar description	Straight length
Busbar trunking polarity	L + N + PE
Number of circuits	1
Number of tap-off outlets	5
Control type	Without
Standards	EN/IEC 61439-6 EN/IEC 60439-2
Width	3140 mm
Depth	30 mm
Height	46 mm
Length	3 m
Net weight	2.4 kg
Quantity per set	Set of 6

Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
IK degree of protection	IK06 conforming to EN/IEC 62262
Ambient air temperature for operation	0...35 °C (100 % of In) 35...40 °C (96 % of In) 40...45 °C (93 % of In) 45...50 °C (89 % of In) 50...55 °C (85 % of In)

Packing Units

Package 1 Weight	2.600 kg
Package 1 Height	0.460 dm
Package 1 width	0.300 dm
Package 1 Length	30.000 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------