

Product data sheet

Characteristics

KBA40ZFU

Canalis, Universal fixing bracket, Canalis KBA, 25 A and 40 A, suspended on threaded rod or lateral, galvanized version



Main

| | |
|---------------------------|---------------------------|
| Range of product | Canalis |
| Product or component type | Bracket |
| Product compatibility | KBA |
| Fixing device mounting | Suspended on threaded rod |
| Maximum load | 60 kg |

Complementary

| | |
|------------------------------------|------------------|
| Accessory / separate part category | Fixing accessory |
|------------------------------------|------------------|

Environment

| | |
|-----------|-------------|
| Standards | IEC 61439-6 |
|-----------|-------------|

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.000 cm |
| Package 1 Width | 3.800 cm |
| Package 1 Length | 7.000 cm |
| Package 1 Weight | 33.000 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 4.000 cm |
| Package 2 Width | 14.500 cm |
| Package 2 Length | 11.000 cm |
| Package 2 Weight | 336.000 g |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 200 |
| Package 3 Height | 18.000 cm |
| Package 3 Width | 24.500 cm |
| Package 3 Length | 38.000 cm |
| Package 3 Weight | 7.100 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|-----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| PVC free | Yes |
| Halogen content performance | Halogen free product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|