

## Product data sheet

### Characteristics

# KBB40ABG44

Feed unit for KBB, Canalis KBB, 40A, left mounting, 2 circuits



#### Main

Range of product	Canalis
Product or component type	Feed unit
Conductors material	Aluminium
[Ie] rated operational current	25 A 40 A
[Ue] rated operational voltage	230...400 V
Number of circuits	2
Protection type	Without protection
Control type	Without

#### Complementary

Provided equipment	End cover
Mounting location	Left
Mounting mode	By clips
Mounting support	Busbar
Connections - terminals	Terminal block - Pg 21 for 6...10 mm <sup>2</sup>
Width	244 mm
Depth	103.5 mm
Height	75.5 mm
Standards	IEC 61439-6 IEC 60439-2

#### Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

#### Contractual warranty

Warranty	18 months
----------	-----------