

## Product data sheet

### Characteristics

# KBB40ABG44

## Canalis - feed unit for KBB - 40A - left mounting - 2 circuits



### Main

Range of product	Canalis
Product or component type	Feed unit
BAR MATERIAL	Aluminium
Product compatibility	KBB
[Ie] rated operational current	25 A 40 A
Mounting location	Left

### Complementary

Protection type	Without protection
[Ue] rated operational voltage	230...400 V
Connections - terminals	Terminal block - Pg 21 for 6...10 mm <sup>2</sup>
Control type	Without
Number of circuits	2
Provided equipment	End cover
Mounting mode	By clips
Mounting support	Busbar
Standards	IEC 61439-6 IEC 60439-2
Width	244 mm
Depth	103.5 mm
Height	75.5 mm



### Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

### Packing Units

Package 1 Weight	0.650 kg
Package 1 Height	0.800 dm
Package 1 width	1.100 dm
Package 1 Length	2.700 dm

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

### Contractual warranty

Warranty	18 months
----------	-----------