

Product data sheet

Characteristics

KBB40ZFU

fixing bracket, Canalis KBB, 25 A and 40 A, suspended on threaded rod or lateral, galvanized version



Main

Range of product	Canalis
Product or component type	Bracket
Product compatibility	KBB
Fixing device mounting	Suspended on threaded rod
Maximum load	60 kg
Quantity per set	Set of 10

Complementary

Accessory / separate part category	Fixing accessory
Width	55 mm
Depth	22 mm
Height	70.5 mm
Net weight	50 g

Environment

Standards	IEC 61439-6
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	5.1 g
Package 1 Height	2.0 cm
Package 1 width	5.5 cm
Package 1 Length	6.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.515 kg
Package 2 Height	5.5 cm
Package 2 width	7 cm
Package 2 Length	13.5 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	220
Package 3 Weight	11.79 kg
Package 3 Height	18 cm
Package 3 width	24.5 cm
Package 3 Length	38 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------