

## Product data sheet

### Characteristics

# KBC16DCB40

Canalis - tap-off unit - 16A - 3L+N+PE - without protection



### Main

Range	Canalis
Product or component type	Tap-off unit
Device short name	KBC
Product compatibility	KBB KBA
Device application	Lighting
Range compatibility	KBA busbar trunking KBB busbar trunking

### Complementary

[Ue] rated operational voltage	230...240 V
[Ui] rated insulation voltage	690 V
[Ie] rated operational current	16 A at 35 °C
Network frequency	50/60 Hz
Protection type	Without protection
Busbar trunking polarity	L2 + L1 + L3 + PE
Tap-off unit polarity	3L+N+PE
Tap-off unit connector type	With fixed polarity
Standards	EN/IEC 60439-2 EN/IEC 61439-6
Width	205 mm
Depth	38 mm
Height	68 mm
Colour	Cream (RAL 9001)
Net weight	90 g

### Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
-------------------------	---------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	189 g
Package 1 Height	8 cm
Package 1 width	8 cm
Package 1 Length	18 cm
Unit Type of Package 2	S03
Number of Units in Package 2	18
Package 2 Weight	3.899 kg
Package 2 Height	30 cm
Package 2 width	30 cm

Package 2 Length	40 cm
Unit Type of Package 3	P06
Number of Units in Package 3	144
Package 3 Weight	40.62 kg
Package 3 Height	80 cm
Package 3 width	80 cm
Package 3 Length	60 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

### Contractual warranty

Warranty	18 months
----------	-----------

