

Product data sheet

Characteristics

KBC16DCB40

Canalis, Tap off unit, Canalis KB, 16A, polarity 3L+N+PE, with phase selection, direct connection



Main

Range	Canalis
Offer type	Control system
Product or component type	Connector
Device application	Lighting Power socket distribution
Range compatibility	Canalis KBA busbar trunking Canalis KBB busbar trunking
[Ie] rated operational current	16 A at 35 °C
[Ue] rated operational voltage	230...240 V
Network frequency	50/60 Hz
Communication port protocol	DALI KNX
Tap-off unit polarity	3L+N+PE
Tap-off unit connector type	With fixed polarity

Complementary

Colour	Cream (RAL 9001)
[Uimp] rated impulse withstand voltage	4 kV
[Ui] rated insulation voltage	690 V
Protection type	Without protection
Width	205 mm
Depth	38 mm
Height	68 mm
Net weight	90 g
Standards	EN/IEC 61439-1 EN/IEC 61439-6

Environment

IP degree of protection	IP55 conforming to EN/IEC 60529
-------------------------	---------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	8.000 cm
Package 1 Length	18.000 cm
Package 1 Weight	189.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	18
Package 2 Height	30.000 cm

Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.899 kg
Unit Type of Package 3	P06
Number of Units in Package 3	144
Package 3 Height	74.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	37.588 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

