

## Product data sheet

### Characteristics

# KZ66

IP 65 seal for 60 x 60 mm front plate and front mounting cam switch - set of 5



### Main

|                                       |  |
|---------------------------------------|--|
| Range of product                      | Harmony Series K1/K2   |
| Accessory / separate part designation | Rubber seal for IP65 degree of protection  |
| Accessory / separate part type        | Seal   |
| Accessory / separate part category    | Protection accessories   |
| Product compatibility                 | K2<br>K1   |
| Accessory / separate part destination | 4 holes front mounting operating head with 60x 60 mm front plate<br>Ø 22 mm front mounting operating head with 60x 60 mm front plate |
| Range compatibility                   | VARIO<br>Mini-VARIO  |
| Material                              | Rubber   |
| Sale per indivisible quantity         | 5  |

### Complementary

|            |          |
|------------|----------|
| Net weight | 0.004 kg |
|------------|----------|

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Weight             | 7 g    |
| Package 1 Height             | 1 cm   |
| Package 1 width              | 11 cm  |
| Package 1 Length             | 15 cm  |
| Unit Type of Package 2       | BAG    |
| Number of Units in Package 2 | 5      |
| Package 2 Weight             | 36 g   |
| Package 2 Height             | 15 cm  |
| Package 2 width              | 1 cm   |
| Package 2 Length             | 11 cm  |
| Unit Type of Package 3       | BB1    |
| Number of Units in Package 3 | 5      |
| Package 3 Weight             | 35 g   |
| Package 3 Height             | 1.7 cm |
| Package 3 width              | 7.7 cm |
| Package 3 Length             | 12 cm  |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|