

Product data sheet

Characteristics

L11/25

Maxi Neutral link, 110 A, 500 V, 11 hole, with cover, front wiring, Black



Main

Range	MAX9
Product brand	Clipsal
Range of product	Blue Point
Product or component type	Neutral link

Complementary

Cable cross section	25 mm ²
[In] rated current	110 A
[Ue] rated operational voltage	500 V
Connector type	Screw terminals
Number of poles	1
Number of mounting holes	11

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	174 g
Package 1 Height	60 mm
Package 1 width	62 mm
Package 1 Length	107 mm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.