

Product data sheet

Characteristics

L11/25BW

Maxi Neutral link, Clipsal - Max 4, 110 A 500 V
11 hole with cover back wiring Black



Main

Range	MAX9
Product brand	Clipsal
Range of product	Blue Point
Product or component type	Neutral link


Complementary

Cable cross section	25 mm ²
[In] rated current	110 A
[Ue] rated operational voltage	500 V
Connector type	Screw terminals
Number of poles	1
Number of mounting holes	11

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6 cm
Package 1 Width	6 cm
Package 1 Length	10.8 cm
Package 1 Weight	175 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	110 cm
Package 2 Width	187 cm
Package 2 Length	206 cm
Package 2 Weight	1.75 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations