

Product data sheet

Characteristics

L11/25BWR

Maxi Active link, 110 A, 500 V, 11 hole, with cover, back wiring, Red



Main

| | |
|---------------------------|-------------|
| Product brand | Clipsal |
| Range of product | Blue Point |
| Product or component type | Active link |




Complementary

| | |
|--------------------------------|--------------------|
| Cable cross section | 25 mm ² |
| [In] rated current | 110 A |
| [Ue] rated operational voltage | 500 V |
| Connector type | Screw terminals |
| Number of poles | 1 |

Packing Units

| | |
|------------------|----------|
| Package 1 Weight | 0.001 kg |
|------------------|----------|

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.