

Product data sheet

Characteristics

L12A

Clipsal MAX4, Mini Neutral link 100 A 500 V 12 hole less cover Black



Main

| | |
|---------------------------|--------------|
| Product brand | Clipsal |
| Range of product | Blue Point |
| Product or component type | Neutral link |




Complementary

| | |
|--------------------------------|-----------------|
| [In] rated current | 100 A |
| [Ue] rated operational voltage | 500 V |
| Connector type | Screw terminals |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.7 cm |
| Package 1 Width | 3.3 cm |
| Package 1 Length | 8 cm |
| Package 1 Weight | 82 g |

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.