

## Product data sheet

### Characteristics

# L12R

## Mini Active link, Clipsal - Max 4, 100 A 500 V 12 hole with cover Red

### Main

|                           |             |
|---------------------------|-------------|
| Range                     | MAX9        |
| Product brand             | Clipsal     |
| Range of product          | Blue Point  |
| Product or component type | Active link |

### Complementary

|                                |                    |
|--------------------------------|--------------------|
| Cable cross section            | 16 mm <sup>2</sup> |
| [In] rated current             | 100 A              |
| [Ue] rated operational voltage | 500 V              |
| Connector type                 | Screw terminals    |
| Number of poles                | 1                  |
| Number of mounting holes       | 12                 |
| Height                         | 86 mm              |
| Width                          | 57 mm              |
| Depth                          | 40 mm              |

### Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Height             | 4.9 cm |
| Package 1 Width              | 8.6 cm |
| Package 1 Length             | 5.7 cm |
| Package 1 Weight             | 113 g  |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| REACH Regulation           |  <a href="#">REACH Declaration</a>      |
| EU RoHS Directive          | Compliant with Exemptions  |
| Mercury free               | Yes  |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a> |
| RoHS exemption information |  <a href="#">Yes</a>                    |
| Circularity Profile        | No need of specific recycling operations   |