

## Product data sheet

### Characteristics

# L16

## Clipsal MAX4, Mini Neutral link 100 A 500 V 16 hole with cover Black



### Main

Range	MAX9
Product brand	Clipsal
Range of product	Blue Point
Product or component type	Neutral link

### Complementary

Cable cross section	16 mm <sup>2</sup>
[In] rated current	100 A
[Ue] rated operational voltage	500 V
Connector type	Screw terminals
Number of mounting holes	16

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	50 cm
Package 1 Width	55 cm
Package 1 Length	85 cm
Package 1 Weight	0.156 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	100 cm
Package 2 Width	130 cm
Package 2 Length	220 cm
Package 2 Weight	1.56 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	100 cm
Package 3 Width	124 cm
Package 3 Length	404 cm
Package 3 Weight	16 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>