

## Product data sheet

### Characteristics

# L18

## Clipsal MAX4, Mini Neutral link 100 A 500 V 18 hole with cover Black



### Main

Range	MAX9
Product brand	Clipsal
Range of product	Blue Point
Product or component type	Neutral link




### Complementary

Cable cross section	16 mm <sup>2</sup>
[In] rated current	100 A
[Ue] rated operational voltage	500 V
Connector type	Screw terminals
Number of poles	1
Number of mounting holes	18
Height	86 mm
Width	57 mm
Depth	40 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	5.6 cm
Package 1 Length	8.4 cm
Package 1 Weight	139 g
Unit Type of Package 2	CAR
Number of Units in Package 2	60
Package 2 Height	25 cm
Package 2 Width	21.4 cm
Package 2 Length	33.8 cm
Package 2 Weight	9.165 kg

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations