

Product data sheet

Characteristics

L5108RELVP

C-BUS 8 CHANNEL ELV RELAY



Main

Range	C-Bus
Product brand	Clipsal

Complementary

[Us] rated supply voltage	15...36 V DC
Connector type	Screw terminals
Width	220 mm
Height	80 mm
Depth	39 mm

Environment

IP degree of protection	IP51
-------------------------	------

Packing Units

Package 1 Weight	441.000 g
Package 1 Height	55.000 mm
Package 1 width	95.000 mm
Package 1 Length	255.000 mm

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.