

Product data sheet

Characteristics

L5108RELVP

Relay, C-Bus, Surface Mounted, Extra Low Voltage, 30 V AC DC, 8 Channel, 2A, Without C-Bus Power Supply



Main

Range of product	C-Bus
Product brand	Clipsal
Range	C-Bus

Complementary

Connector type	Screw terminals
[Us] rated supply voltage	15...36 V DC
Width	220 mm
Height	80 mm
Depth	39 mm

Environment

IP degree of protection	IP51
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	9 cm
Package 1 Length	25.5 cm
Package 1 Weight	427 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	30 cm
Package 2 Width	28.5 cm
Package 2 Length	39 cm
Package 2 Weight	9.707 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	320
Package 3 Height	116 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	142.038 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins