

Product data sheet

Characteristics

L5504RVF20

Clipsal C-Bus, Relay, DIN Rail Mounted,
Voltage Free, 240V AC, 4 Channel, 20A, With
C-Bus Power Supply



Main

Range	C-Bus
Product brand	Clipsal







Complementary

[Us] rated supply voltage	15...36 V DC
Device composition	Socket-outlet
Connector type	Screw terminals
Width	215 mm
Height	85 mm
Depth	65 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	10.5 cm
Package 1 Length	22 cm
Package 1 Weight	631 g
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	24.5 cm
Package 2 Width	21 cm
Package 2 Length	34 cm
Package 2 Weight	4.063 kg
Unit Type of Package 3	P12
Number of Units in Package 3	180
Package 3 Height	95 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	130.89 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins