

Product data sheet

Characteristics

L5508RVFP

RELAY C-BUS 8 CH 10A DIN LEARN



Main

Range	C-Bus
Product brand	Clipsal





Complementary

[Us] rated supply voltage	15...36 V DC
Device composition	Socket-outlet
Connector type	Screw terminals
Width	215 mm
Height	85 mm
Depth	65 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	770 g
Package 1 Height	9.69 cm
Package 1 width	10.837 cm
Package 1 Length	22.884 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Weight	5.1 kg
Package 2 Height	22.2 cm
Package 2 width	24.8 cm
Package 2 Length	34.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
