

Product data sheet

Characteristics

L5512RVFP

Clipsal C-Bus, Relay, DIN Rail Mounted, Voltage Free, 240V AC, 12 Channel, 10A, Without C-Bus Power Supply



Main

Range	C-Bus
Product brand	Clipsal



Complementary

[Us] rated supply voltage	15...36 V DC
Network type	AC/DC
Device composition	Socket-outlet
Connector type	Screw terminals
Width	215 mm
Height	85 mm
Depth	65 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.573 cm
Package 1 Width	10.8 cm
Package 1 Length	22.796 cm
Package 1 Weight	861.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	22.6 cm
Package 2 Width	24.6 cm
Package 2 Length	35.2 cm
Package 2 Weight	5.571 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins