


Product data sheet

Characteristics

LA4DE3E

TeSys; TeSys Deca, suppressor module, varistor, 24...48 V DC



Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	4P LP1D80 3P LC1D80...D95

Complementary

Mounting location	Top
Mounting mode	By screws
Suppressor technology	Varistor (peak limiting)
[Uc] control circuit voltage	24...48 V DC
Maximum peak voltage	2 Uc
Net weight	0.018 kg

Environment

Standards	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 60947-5-1 UL 60947-5-1 GB/T 14048.5
Product certifications	UL[RETURN]CSA
IP degree of protection	IP2X conforming to IEC 60529
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	4.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	16.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	78
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.455 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------