


Product data sheet

Characteristics

LA4DE3U

TeSys D - suppressor module - varistor - 110...250 V DC



Main

Range	TeSys
Device short name	LA4D
Product or component type	Suppressor module
Product compatibility	4P LC1D40008...D80008 3P LC1D80...D95 4P LP1D80004

Complementary

Mounting location	Top
Mounting mode	By screws
Suppressor technology	Varistor (peak limiting)
[Uc] control circuit voltage	110...250 V DC
Maximum peak voltage	2 Uc
Net weight	0.018 kg

Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16 g
Package 1 Height	2.9 cm
Package 1 width	4.3 cm
Package 1 Length	5.2 cm
Unit Type of Package 2	S01
Number of Units in Package 2	32
Package 2 Weight	768 g
Package 2 Height	15 cm
Package 2 width	15 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------