

Product data sheet

Characteristics

LA4SKC1U

TeSys SK - suppressor module - diodes - 24...250 V DC



Main

Range	TeSys
Device short name	LA4SK
Product or component type	Suppressor module
Product compatibility	CA2SK LC1SK06 CA3SK LP1SK06 LC1SKGC
Suppressor technology	Diodes
Quantity per set	Set of 10

Complementary

Mounting location	Right hand side
[Uc] control circuit voltage	24...250 V DC
Maximum peak voltage	1 Uc
Product weight	0.003 kg

Environment

Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-50...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3 g
Package 1 Height	3.5 cm
Package 1 width	6 cm
Package 1 Length	14.3 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	30 g
Package 2 Height	3.5 cm
Package 2 width	6 cm
Package 2 Length	14.3 cm
Unit Type of Package 3	S01
Number of Units in Package 3	190
Package 3 Weight	773 g
Package 3 Height	15 cm
Package 3 width	15 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------