

Product data sheet

Characteristics

LA4SKE1U

TeSys; TeSys SK, suppressor module, varistor, 110...250 V AC/DC



Main

| | |
|---------------------------|---|
| Range | TeSys |
| Device short name | LA4SK |
| Product or component type | Suppressor module |
| Product compatibility | LC1SK06 LP1SK06 CA2SK LC1SKGC CA3SK |
| Suppressor technology | Varistor (peak limiting) |
| Quantity per set | Set of 10 |

Complementary

| | |
|------------------------------|----------------------------------|
| Mounting location | Right hand side |
| [Uc] control circuit voltage | 110...250 V AC 110...250 V DC |
| Maximum peak voltage | 2 Uc |
| Net weight | 0.003 kg |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -20...50 °C |
| Ambient air temperature for storage | -50...70 °C |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4.0 cm |
| Package 1 Width | 5.0 cm |
| Package 1 Length | 12.0 cm |
| Package 1 Weight | 3.0 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 4.0 cm |
| Package 2 Width | 5.0 cm |
| Package 2 Length | 12.0 cm |
| Package 2 Weight | 36.0 g |
| Unit Type of Package 3 | S01 |
| Number of Units in Package 3 | 190 |
| Package 3 Height | 15.0 cm |
| Package 3 Width | 15.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 870.0 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|