

Product data sheet

Characteristics

LA9RM201

Harmony Control Relays, Probe for liquid level control, maximum operating temperature 100 degree C



Main

Range of product	Harmony Control Relays
Product or component type	Level control probe
Accessory / separate part designation	Probe for liquid level control
Accessory / separate part destination	Liquid level control relay
Accessory / separate part category	Relay accessories
Product compatibility	RM84 RM4L RM35LM

Complementary

Diameter	16 mm
Length	150 mm
Type of installation	Cable suspension
Net weight	0.1 kg



Environment

Maximum ambient air temperature for operation	100 °C
---	--------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	15.5 cm
Package 1 Length	2.6 cm
Package 1 Weight	93.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.909 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------
