

## Product data sheet

### Characteristics

# LE2D12B7

TeSys LE - enclosed DOL reversing starter - 12 A - 24 V AC coil



### Main

Range	TeSys
Product name	TeSys LE
Device short name	LE2D
Product or component type	Enclosed DOL reversing starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Reversing contactor
[Ie] rated operational current	12 A AC-3
Motor power kW	3 kW at 220/230 V AC 50/60 Hz 7.5 kW at 500 V AC 50/60 Hz 7.5 kW at 660/690 V AC 50/60 Hz 5.5 kW at 380/400 V AC 50/60 Hz 5.5 kW at 415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz
[Ithe] conventional enclosed thermal current	12 A
[Uc] control circuit voltage	24 V AC 50/60 Hz
Control type	Push-button stop/reset red O Selector switch 2 positions start I-II

### Complementary

Cable entry number	2 ISO20 top 2 ISO25 top 2 Pg 16 bottom 2 Pg 21 bottom 2 ISO20 bottom 2 ISO25 bottom
Width	101 mm
Height	201 mm
Depth	160 mm
Net weight	2.1 kg

### Environment

Material	Polycarbonate
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.1 kg
Package 1 Height	26 cm
Package 1 width	29 cm
Package 1 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------