

## Product data sheet

### Characteristics

# LZ1H6X5BD

## Starter TeSys H 3kW-400V control 24VDC



### Main

Range	TeSys
Product name	TeSys H
Device short name	LZ1H
Product or component type	Ultra-compact starter
Motor starter type	Direct on line
Poles description	3P
[Ue] rated operational voltage	500 V AC
[Ie] rated operational current	6.5 A at 500 V AC-53A 9 A at 500 V AC-51 5 A at 500 V AC-53A mounting side by side 7 A at 500 V AC-51 mounting side by side
Thermal protection adjustment range	1.5...9 A
Motor power kW	1.5 kW at 220 V AC 0.65 1.5 kW at 230 V AC 0.65 2.2 kW at 380 V AC 0.65 3 kW at 400 V AC 0.65 3 kW at 415 V AC 0.65 3 kW at 440 V AC 0.65 3 kW at 500 V AC 0.65
Motor power hp	1 Hp at 200 V AC 1.5 Hp at 230 V AC 3 hp at 460 V AC
[Uc] control circuit voltage	24 V DC
Thermal overload class	Class 10A conforming to IEC 60947-4-2

### Complementary

Auxiliary contact composition	1 C/O fault signalling
Control circuit voltage limits	19.2...30 V DC
Current consumption	<= 40 mA at 24 V DC
Reset	Manual Automatic reset Electrical reset
Electrical durability	30 Mcycles
Maximum operating rate	120 Cyc/Mn AC-51 50 % ON 6 cyc/mn AC-53A 50 % ON
Mounting mode	By clips
Mounting support	DIN rail
Connections - terminals	Screw clamp terminals 1 cable(s) 0.2...2.5 mm <sup>2</sup> - rigid Screw clamp terminals 1 cable(s) 0.25...2.5 mm <sup>2</sup> - flexible - with cable end Screw clamp terminals 1 cable(s) 0.2...2.5 mm <sup>2</sup> - flexible - without cable end
Tightening torque	0.5...0.6 N.m flat Ø 2.5 mm screwdriver 3 mm
Certifications	CULus CE
Standards	IEC 60947-4-2 UL 60947-4-1
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV

Pollution degree	2
Width	22.5 mm
Height	99 mm
Depth	114.5 mm
Net weight	212 g

## Environment

IP degree of protection	IP20
Protective treatment	TC
Ambient air temperature for operation	-25...30 °C without derating 30...70 °C with derating
Ambient air temperature for storage	-40...80 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	250 g
Package 1 Height	3.6 cm
Package 1 width	11.7 cm
Package 1 Length	12 cm
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Weight	2.71 kg
Package 2 Height	15 cm
Package 2 width	15 cm
Package 2 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins