

Product data sheet

Characteristics

MB224CM2

Acti 9 - MB ISOBAR Standard Distribution Board 24P C60 IP42 W/250A Grey



Main

Range	Acti 9
Product name	Acti 9 isobar DB
Device short name	MB
Product or component type	Distribution board
Device application	Distribution
Enclosure type	Standard
Door type	External plain
Provided equipment	Pole filler Circuit schedule card Enclosure Door DIN rail Removable gland plates Keys Chassis 2 earth/neutral terminal block - top and bottom 165 A Mounting plate
Colour	Grey

Complementary

[Ie] rated operational current	250 A
Enclosure mounting	Surface
Poles description	3P + N
Enclosure material	Steel
Number of ways	24 ways (outgoer) - 1P with 18 mm
Enclosure material	steel
Height	750 mm
Width	580 mm
Depth	235 mm
Internal depth	168.7 mm
IP degree of protection	IP42

Packing Units

Package 1 Weight	1.000 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.