

## Product data sheet

### Characteristics

# MB260E30

MB Encapsulated distribution board, Acti9, 60 poles, 250A no main switch, 18mm, IP42, grey



### Main

|                           |  |
|---------------------------|--|
| Range                     | Acti9  |
| Product name              | Acti9 encapsulated DB  |
| Device short name         | MB   |
| Product or component type | Distribution board   |
| Device application        | Distribution   |
| Enclosure type            | Standard   |
| Door type                 | External plain   |
| Provided equipment        | Pole filler<br>Circuit schedule card<br>Enclosure<br>Door<br>Removable gland plates<br>Keys<br>Chassis<br>2 earth/neutral terminal block - top and bottom<br>165 A<br>DIN rail |
| Colour                    | Grey   |

### Complementary

|  |            |
|--|------------|
| [Ue] rated operational voltage         | 415 V      |
| Network frequency                      | 50 Hz      |
| [Ie] rated operational current         | 250 A      |
| Breaking capacity                      | 25 kA      |
| [Ui] rated insulation voltage          | 500 V      |
| [Uimp] rated impulse withstand voltage | 6 kV       |
| Enclosure mounting                     | Surface    |
| Poles description                      | 3P + N     |
| Enclosure material                     | Steel      |
| Outgoer Pole capacity                  | 60 x 18 mm |
| Enclosure material                     | steel      |
| Height                                 | 1200 mm    |
| Width                                  | 580 mm     |
| Depth                                  | 235 mm     |
| IP degree of protection                | IP42       |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | Db       |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 25.0 cm  |
| Package 1 Width              | 122.0 cm |
| Package 1 Length             | 59.0 cm  |
| Package 1 Weight             | 51.0 kg  |

### Offer Sustainability

|                   |  |
|-------------------|--|
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
|-------------------|--|