

Product data sheet

Characteristics

MB260EH0

Acti9, MB Encapsulated distribution board,
Acti9, 60 poles, 250A no main switch,
18/27mm, IP42, grey



Main

Range	Acti9
Product name	Acti9 encapsulated DB
Device short name	MB
Product or component type	Distribution board
Device application	Distribution
Enclosure type	Standard
Door type	External plain
Provided equipment	Earth/Neutral terminal block 165 A Pole filler Circuit schedule card Removable gland plates - top and bottom 2 keys Enclosure Door SAU chassis DIN rail
Colour	Grey

Complementary

[Ue] rated operational voltage	415 V
Network frequency	50 Hz
[Ie] rated operational current	250 A
Breaking capacity	25 kA
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Enclosure mounting	Surface
Poles description	3P + N
Enclosure material	Steel
Outgoer Pole capacity	12 x 27 mm 48 x 18 mm
Enclosure material	steel
Height	1200 mm
Width	580 mm
Depth	235 mm
IP degree of protection	IP42

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25 cm
Package 1 Width	60 cm
Package 1 Length	121 cm
Package 1 Weight	41 kg