

Product data sheet

Characteristics

MCB6-106

Miniature circuit breaker, MAX4, 1P, 6 A, B curve, 6000 A, 240 V



Main

Product brand	Clipsal
---------------	---------

Complementary

Curve code	B
Number of poles	1
[In] rated current	6 A
Number of modules	1
[Ue] rated operational voltage	240 V
Breaking capacity	6 kA conforming to EN 60898
Network type	AC
Network frequency	50/60 Hz



Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-5...40 °C
Standards	IEC 60898
Product certifications	CE: N17682 ACMA: N11193 RCM: N5400

Packing Units

Package 1 Weight	103.600 g
Package 1 Height	72.000 mm
Package 1 width	85.000 mm
Package 1 Length	18.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
