

Product data sheet

Characteristics

MCB6-140

Clipsal - Max 4, Miniature Circuit Breakers, C - Curve, 1 Pole, 1 Module, 240V, 40A, 6KA



Main

Product brand	Clipsal
---------------	---------

Complementary

Curve code	B
Number of poles	1
[In] rated current	40 A
Number of modules	1
[Ue] rated operational voltage	240 V
Breaking capacity	6 kA conforming to EN 60898
Network type	AC
Network frequency	50/60 Hz




Environment

IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-5...40 °C
Standards	IEC 60898
Product certifications	CE: N17682 ACMA: N11193 RCM: N5400

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	118.5 g

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes