

## Product data sheet

### Characteristics

# MDECLERGM450

## Clipsal - Cable Management, Grp Class A External 90 Degree Riser, 450mm Wide



### Main

Product brand	Clipsal
---------------	---------

### Complementary

Type of side joist	Flat
Type of rung	Flat
Operating angle	90 °
Width	Cable ladder: 450 mm
Material	Glass reinforced plastic

### Environment

Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>