

Product data sheet

Characteristics

MDECLERGN300

GN CBL LAD 90D Ext Riser, Clipsal - Cable Management, 300mm



Main

Product brand	Clipsal
---------------	---------

Complementary

Type of side joist	Flat
Type of rung	Flat
Operating angle	90 °
Width	Cable ladder: 300 mm
Material	Glass reinforced plastic

Environment

Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations