

## Product data sheet

### Characteristics

# MDECLGHL300150

## Clipsal - Cable Management, Series C CC

### Cable Ladder 300 mm Wide 6M

#### Main

Product brand	Clipsal
Range of product	Series C

#### Complementary

Type of rung	Flat
Fixing mode	By bolt By nut
Height	150 mm
Width	300 mm
Length	6 m
Practical load capacity	1461.19 N
Material	Glass reinforced plastic

#### Environment

Ambient air temperature for operation	-140...120 °C
---------------------------------------	---------------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.